

WET LOCATION CYLINDERS

Add security, energy efficiency and style to exteriors with these modern cylinders.

These stylish, sleek round and square cylinders provide an elegant and versatile solution for outdoor lighting needs.

LED or PAR light source options direct light up and down and offer beautiful, glare-free illumination.




ROUND



SQUARE



 A **wet-location rated lens** is included, making the fixture ready for wet-location use right out of the box.

FINISHES

- Antique Bronze - 020
- Black - 031



APPLICATIONS:

- Covered porch
- Foyer
- Patio
- Barn
- Deck
- Garage
- Entryway

WET LOCATION CYLINDERS

Round Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560290-020 P560290-031	Antique Bronze Black	Up/down cylinder	5" W., 7-1/4" ht.	2 PAR30 75w
P560292-020 P560292-031	Antique Bronze Black	Up/down cylinder	6" W., 18" ht.	2 PAR38 250w

All fixtures:



P560290-020
P560291-020-30



P560290-031
P560291-031-30

Round LED Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560291-020-30 P560291-031-30	Antique Bronze Black	Up/down cylinder	5" W., 7-1/4" ht.	37.2W integrated LED 3000K, 90CRI, 730 delivered lumens
P560293-020-30 P560293-031-30	Antique Bronze Black	Up/down cylinder	6" W., 18" ht..	64W integrated LED 3000K, 90CRI, 1833 delivered lumens

All fixtures:



P560292-020
P560293-020-30



P560292-031
P560293-031-30



Wet location lens included.

Square Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560294-020 P560294-031	Antique Bronze Black	Up/down cylinder	6" W., 18" ht.	2 PAR38 250w,

All fixtures:



P560294-020
P560295-020-30



P560294-031
P560295-031-30

Square LED Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560295-020-30 P560295-031-30	Antique Bronze Black	Up/down cylinder	6"W, 18" ht.	64W integrated LED 3000K, 90CRI, 3641 delivered lumens

All fixtures:



Wet location lens included.