



SADDLE-BOX® NONMETALLIC CEILING FAN SUPPORT BOXES

4" Round for Nonmetallic Sheathed Cable


Application

RACO® SADDLE-BOX® 7120 series boxes are specifically designed for use in ceiling fan support or heavy lighting fixture applications. The unique U-shaped design allows box to mount on any standard 1-1/2" wide joist.

The 7120VB prevents unwanted penetration of exterior air and helps maintain the existing interior environment from elements outside the structure.

Features

- Large 12.5 cu. in. wiring compartment
- For 1/2", 5/8", or 3/4" drywall
- Patented design
- Patented, nonmetallic cable clamps (no need for separate connector)
- 2 hour fire rating
- Fan/Fixture mounting hardware hidden behind protective decal until ready for mounting. Screw heads are not exposed to drywall mud and paint
- Vapor/air barrier flange (7120VB) with integral wire entry seal provide energy savings and quick installation for new work applications
- UL Listed



7120-1 & 7120



7120VB

Catalog No.	Description	Cable Clamps	Box Cu. In. Cap.	Std. Pkg.	UPC-A Bar Code	Recommended Maximum Support Loads	
						Ceiling Fan (Dynamic) Lbs.	Fixture (Static) Lbs.
7120-1	SADDLE-BOX®	4	12.5	24	050169712016	70	210
7120	SADDLE-BOX®	4	12.5	20*	050169071205	70	210
7120VB	SADDLE-BOX®, Vapor Barrier	4	12.5	24	050169999714	70	210

*Packaged in a stackable, individual chipboard carton suitable for shelf display.

U.S. Patents 4,874,905; 4,605,816; 4,580,689; 5,234,119