



# Power and AV Wall Boxes

## Wall Boxes

Power, data, interfaces and more will mount discretely behind the flat screen. Covers are available in white or black. Supplied with mounting screws for wood or steel stud, grounding screws, tie wraps, and rubber grommets. Two of the single gang knockouts have a 1" by 2" oblong internal knockout and can be used with the supplied grommets. The flush box installation allows flat panel displays and interactive "smart" boards to sit flush against the wall with no dangling cords.

### FEATURES

- Low voltage conduit feed-thru for connectorized cables with 1", 1½" and 2" knockouts
- ¾" extension available for concrete block walls
- Two-piece paintable cover allows for better cable management
- Boxes conform to UL 62368-1:2019 Ed.3, Certified to CSAC22.2 #62368-1:2019 Ed.3

## Wall Enclosure

2 and 4-Gang Flat Panel Television (FPTV) connection enclosure delivers high density connectivity and power in the wall. This allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords. It quickly installs to studs or sheetrock without additional components or hardware.

- Optional screw on cover reduces tampering
- cULus 1863 Listed

### BOX DESIGN AND MOUNTING

- Flush installation against walls
- Sheet metal base, white powder coat finish
- Accepts standard electrical boxes
- Integrated cable management
- Multiple device mounting options
- 1½" and 1¼" conduit knockouts
- Easily mounts to studs or Sheetrock
- Easily replaceable receptacle
- Trim ring covers rough-in



**HRWB25WHT with 2" Low Voltage Feed-Thru**



**HRWB25WHT**



**HRWB25WHT with HRW25BE075**



**NSAV124M**



**NSAV62M**





## WALL BOXES

Description	Height	Width	Depth	Cover Colour	Catalogue Number
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	White	<b>HRWB25WHT</b>
HRWB25WHT replacement cover	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	White	<b>HRWB25WHTRC</b>
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	Black	<b>HRWB25BLK</b>
HRWB25BLK replacement cover	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	Black	<b>HRWB25BLKRC</b>
HRWB25 series wall box w/ 3/4" extension	7.47" (189.7)	14.50" (368.3)	0.75" (19.1)	Steel	<b>HRWB25BE075</b>



## POWER KITS

Description	Colour	Catalogue Number
Standard power kit	White	<b>NSOKPTR</b>
Surge protected power kit	White	<b>NSOKPS</b>

## AV CONNECTORS AND PLATES

Description	Colour	Catalogue Number
1-Gang 6-Port plate	White	<b>IFP16W</b>
1-Gang Hubbell iSTATION plate	White	<b>IMF1W</b>
Category 6 Jack	White	<b>HXJ6W</b>
HDMI Feed-Thru	White	<b>SFHC14W</b>



IFP16W



NSOKPS



IMF1W



HXJ6W



SFHC14W



## FPTV CONNECTION ENCLOSURE

Description	Colour	Catalogue Number
2-Gang in-wall enclosure	White	<b>NSAV62M</b>
Steel cover for NSAV6 series	White	<b>NSAV6C</b>
4-Gang in-wall enclosure	White	<b>NSAV124M</b>
Steel cover for NSAV12 series	White	<b>NSAV12C</b>



NS801W



NSAV6C

## POWER KITS

Description	Colour	Catalogue Number
Standard power kit	White	<b>NSOKPTR</b>
Surge protected power kit	White	<b>NSOKPS</b>

## AV CONNECTORS AND PLATES

Description	Colour	Catalogue Number
1-Gang blank plate	White	<b>P14W</b>
1-Gang decorator plate	White	<b>P26W</b>



NSOKPS



SFHC14W



NSJ6W

For additional options and technical information, please see our full line catalogue.

©2024 Hubbell Incorporated. All rights reserved. Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.

Hubbell Canada | 870 Brock Rd South, Pickering, ON L1W 1Z8  
hubbell.ca | 800-465-7051



A proud member of the Hubbell Family.

WDK\_SF-01086\_CanEN\_V1  
01/24