



# WIEGMANN<sup>®</sup>

Commercial and Industrial Enclosures



**NEW!**

## ULTIMATE<sup>®</sup> *Wall Mount Enclosure with Removable Gland Plate*



PROTECT  
FROM



*The newest addition to WIEGMANN'S ULTIMATE<sup>®</sup> Series line of wall mount enclosures features a removable gland plate on the bottom of the enclosure. The fully gasketed gland plate can be removed for easy drilling and hole tapping without disturbing the integrity of the enclosure. Designed for harsh environments where dust, water and other contaminants are a problem.*

### **Features**

- Fully gasketed gland plate on the bottom of the enclosure can be easily removed
- Bodies, doors and gland plates are fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Quarter-turn semi-flush latch hold the door securely closed
- Doors are sealed with a poured in place gasket
- Studs for mounting optional *Ultimate* Series back panels are provided

### **Industry Standards**

UL508A Listed; Types 3R, 4, 12 & 13  
cUL Listed per CSA C22.2 No. 14; Type 3R,  
4, 12 & 13  
NEMA/EEMAC Type 3R, 4, 12 & 14

**Contact your sales representative today for pricing and ordering details.**

## Wall Mount Enclosures with Removable Gland Plate

Catalog Number	Description	Dimensions H x W x D	Replacement Gland Plate	Back Panel*
N412121206CGP	N412 SGL DR ULTM W/GP 12 x 12 x 6 CS-GRY	12 x 12 x 6	GP1206	NP1212C
N412161206CGP	N412 SGL DR ULTM W/GP 16 x 12 x 6 CS-GRY	16 x 12 x 6	GP1206	NP1612C
N412161606CGP	N412 SGL DR ULTM W/GP 16 x 16 x 6 CS-GRY	16 x 16 x 6	GP1606	NP1616C
N412201606CGP	N412 SGL DR ULTM W/GP 20 x 16 x 6 CS-GRY	20 x 16 x 6	GP1606	NP2016C
N412161608CGP	N412 SGL DR ULTM W/GP 16 x 16 x 8 CS-GRY	16 x 16 x 8	GP1608	NP1616C
N412201608CGP	N412 SGL DR ULTM W/GP 20 x 16 x 8 CS-GRY	20 x 16 x 8	GP1608	NP2016C
N412202008CGP	N412 SGL DR ULTM W/GP 20 x 20 x 8 CS-GRY	20 x 20 x 8	GP2008	NP2020C
N412242408CGP	N412 SGL DR ULTM W/GP 24 x 24 x 8 CS-GRY	24 x 24 x 8	GP2408	NP2424C
N412242410CGP	N412 SGL DR ULTM W/GP 24 x 24 x 10 CS-GRY	24 x 24 x 10	GP2410	NP2424C
N412242412CGP	N412 SGL DR ULTM W/GP 24 x 24 x 12 CS-GRY	24 x 24 x 12	GP2412	NP2424C
N412302408CGP	N412 SGL DR ULTM W/GP 30 x 24 x 8 CS-GRY	30 x 24 x 8	GP2408	NP3024C
N412302410CGP	N412 SGL DR ULTM W/GP 30 x 24 x 10 CS-GRY	30 x 24 x 10	GP2410	NP3024C
N412302412CGP	N412 SGL DR ULTM W/GP 30 x 24 x 12 CS-GRY	30 x 24 x 12	GP2412	NP3024C
N412362408CGP	N412 SGL DR ULTM W/GP 36 x 24 x 8 CS-GRY	36 x 24 x 8	GP2408	NP3624C
N412362410CGP	N412 SGL DR ULTM W/GP 36 x 24 x 10 CS-GRY	36 x 24 x 10	GP2410	NP3624C
N412362412CGP	N412 SGL DR ULTM W/GP 36 x 24 x 12 CS-GRY	36 x 24 x 12	GP2412	NP3624C
N412363012CGP	N412 SGL DR ULTM W/GP 36 x 30 x 12 CS-GRY	36 x 30 x 12	GP3012	NP3630C
N412363612CGP	N412 SGL DR ULTM W/GP 36 x 36 x 12 CS-GRY	36 x 36 x 12	GP3612	NP3636C

\*Back panels must be ordered separately

### REPLACEMENT GLAND PLATES

Catalog Number	Description
GP1206	GLAND PLATE 12X6 CS-GRY
GP1606	GLAND PLATE 16X6 CS-GRY
GP1608	GLAND PLATE 16X8 CS-GRY
GP2008	GLAND PLATE 20X8 CS-GRY
GP2408	GLAND PLATE 24X8 CS-GRY
GP2410	GLAND PLATE 24X10 CS-GRY
GP2412	GLAND PLATE 24X12 CS-GRY
GP3012	GLAND PLATE 30X12 CS-GRY
GP3612	GLAND PLATE 36X12 CS-GRY



**COMMERCIAL  
CONSTRUCTION**  
A Division of Hubbell Incorporated (Delaware)

© 2020 Hubbell. All rights reserved. Information subject to change.  
Trademarks are property of their respective owners.

Hubbell Canada Inc.  
905-839-1138

Hubbell de Mexico, S.A. de C.V.  
52-55-9151-9999

**Wiegmann**  
Freeburg, IL 62243  
618-539-3193

[hubbell.com/wiegmann/en](http://hubbell.com/wiegmann/en)

**WIEGMANN®**

WG\_SEL\_021\_GLND-PLT  
1/2020