



LJT

LED troffer

OFFICE
RETAIL
SCHOOL

EASY on the budget

LJT is rebate friendly for attainable LED lighting. Projects will run smoothly and stay on track within your resources.

EASY to use rebates

Take advantage of utility rebates for even greater cost effectiveness.

- 2x4—Save up to 25% energy
- 1x4 and 2x2—Save up to 26% energy
- DLC® (DesignLights Consortium) Qualified, with some Premium Qualified configurations - see www.designlights.org

EASY on the contractor

LJT is designed as a one-for-one replacement for fluorescent lensed troffers.

- 1x4, 2x2 and 2x4
- Grid, surface, or cable mount

EASY on the project

LJT offers on/off, step-dimming, 0-10V continuous dimming, flex, integral emergency battery pack, IC rating and all the options you need to make the project work.

EASY on the distributor

LJT is stocked in the Hubbell Lighting Regional Distribution Centers.

EASY on the owner

Change your lamps only **once every 12 years** with LJT's 60,000 hour rated life*.

- L80 lumen maintenance
- 4 LED color choices with excellent color consistency and 82 CRI
- 5 year warranty

LJT		-					-	
MODEL		COLOR TEMP	CEILING TYPE	SHIELDING		DRIVER	OPTIONS	
LJT LED Lensed Troffer		30 3000K 35 3500K 40 4000K 50 5000K	G Grid ¹ SM Surface Mount CM Cable Mount ²	A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal A12F Pattern 12 Frosted Acrylic Lens A12125F Pattern 12 Frosted Acrylic Lens, 0.125" Nominal A19 Pattern 19 Acrylic Lens, 0.156" Nominal A19F Pattern 19 Frosted Acrylic Lens .156"	E Fixed Output ED 0-10V Dimming ED1 0-10V 1% Dimming EDD 0-10V Dimming, Dim to Dark ⁴ ESD Step Dimming ^{4,5} LUTH Hi-Lume 1% EcoSystem LED driver with Soft-on, Fade-to-Black dimming technology ^{4,5}	ELL14 Emergency Battery Pack Installed, 1400 Lumen ^{5,6,7} GLR Fast Blow Fuse GTD Generator Transfer Device ^{5,8} DTS Dimming Bypass Module ^{5,9} C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex G1 Single Gasketing (Door to Housing) G2 Double Gasketing (G1 and Lens to Door) G3 Triple Gasketing (G2 and Housing to Ceiling) F02 End-Frame (CM/CM only)		
SIZE	LUMEN OUTPUT	DOOR						
14 1' x 4'	XW Extra Low Watt (1x4, 2x4) VW Very Low Watt MW Medium Low Watt LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen XL Extra High Lumen ⁵ (2x4 only)	FS White Flush Steel FA White Flush Aluminum RA Regressed Aluminum ³						
See Product Availability table.								



HUBBELL
Lighting