



* Representative image

Anchor, PISA 4, 14in, 1in threads

by CHANCE Utility
Catalog ID: 024484

Standard Strength Anchor Helix.- 4,000 Ft Lbs (5,424 N-M), 14" (355 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

- Installed with Chance anchor wrench C1021583
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

Product Details

General

Coating	Painted
Number of Helices	1
Torque Rating	4000 ft-lbs
Type	Anchor Helix
UPC	096359209683

Dimensions

Anchor Helix Diameter(s)	14 in
Anchor Hub Size	1.375 in
Rod Diameter	• 0.750 • 1.000 in
Weight	21.991 lb

Certifications and Compliance

Industry Standard(s)	RUS Accepted
----------------------	--------------

Logistics

Pallet Quantity	48 EA
Standard Package	2

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com