



* Representative image

SCREW, THIMBLEYE, 5/8in x 6 3/4in

by CHANCE Utility
Catalog ID: 09931

Thimbleye screw, 5/8" diameter gimlet thread, 6 3/4" long shank below the eye with 3" thread length. Internal eye is 1 1/2" x 1 5/8". Galvanized per ASTM A-153.

Product Details

General

| | |
|----------|-------------------------|
| Coating | Galvanized, ASTM A-153 |
| Material | Steel |
| Style | Lag Screw, Gimlet Point |
| Type | Thimbleye Bolts |
| UPC | 096359066989 |

Dimensions

| | |
|------------------------|---------|
| Diameter | 0.63 in |
| Diameter (Fraction) | 5/8 in |
| Distance From Pole | N/A |
| Length | 6.75 in |
| Length - Threaded Area | 3 |
| Weight | 1.1 lb |

Logistics

| | |
|-----------------|---------|
| Pallet Quantity | 1680 EA |
|-----------------|---------|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com