




INSULATED BUSHINGS

Insulated Bushings Malleable Iron
N/A

B41



Catalog #: 1138

APPLICATIONS

For use on threaded rigid/IMC conduit to provide a smooth rounded surface at the entrance of raceways
N/A

PRODUCT FEATURES

Insuliner temperature rated at 150 degrees Celsius
Malleable iron construction insures mechanical protection for the raceway
Zinc electro plated for added corrosion protection
1/2 in. to 1 in. trade sizes are also available in die cast zinc

UL LISTED

Standard 514B, UL Listed E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 2 in.

DRAWING DIMENSIONS

Dimension A: 2-23/32 in.
Dimension B: 23/32 in.
Dimension C: 1-61/64 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 10
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 34.00
Ship Carton Length (in.): 6.25
Ship Carton Width (in.): 4.50
Ship Carton Height (in.): 4.25
Ctn Weight (Lbs.): 3.40
UPC Number: 050169011386
I2of5: 50050169011381