




## SEALING LOCKNUTS

### Sealing Locknuts Steel

B38



Catalog #: 1204

#### APPLICATIONS

For use on threaded rigid/IMC conduit to provide a liquidtight seal against water and oil  
RACO sealing locknuts may be used with either sheet metal or cast enclosures

#### PRODUCT FEATURES

- Fused-in-place gasket guarantees a liquidtight seal
- Use RACO sealing locknuts as an economical alternative to a threaded enclosure connector
- All steel construction insures mechanical protection
- Zinc electro plated for corrosion protection
- N/A

#### UL LISTED

Standard 514B (part numbers 1202-1210), UL File E195969

#### CSA

C22.2 No. 18 (part numbers 1202-1211)

#### COMPLIANCES

MSDS  
[www.hubbell-rtb.com/certifications/Hubbell-RACO\\_MSDS\\_for\\_WP\\_Boxes\\_and\\_Fittings,January\\_2015.pdf](http://www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf)

#### GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

#### DRAWING DIMENSIONS

Dimension A: 1-23/32 in.  
 Dimension B: 1-17/64 in.  
 Thread Spec. C: 1 in. - 11-1/2 NPT  
 Dimension D: 1/4 in.

#### PACKAGING

Package Type: Carton  
 Ship Carton Qty.: 50  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 4.20  
 Ship Carton Length (in.): 6.25  
 Ship Carton Width (in.): 4.50  
 Ship Carton Height (in.): 4.25  
 Ctn Weight (Lbs.): 2.10  
 UPC Number: 050169012048  
 I2of5: 50050169012043