


**SEALING LOCKNUTS**Sealing Locknuts Steel
N/A**B38**

Catalog #: 1207

APPLICATIONS

For use on threaded rigid/IMC conduit to provide a liquidtight seal against water and oil
 RACO sealing locknuts may be used with either sheet metal or cast enclosures

PRODUCT FEATURES

Fused-in-place gasket guarantees a liquidtight seal
 Use RACO sealing locknuts as an economical alternative to a threaded enclosure connector
 All steel construction insures mechanical protection
 Zinc electro plated for corrosion protection
 N/A

UL LISTED

Standard 514B (part numbers 1202-1210), UL File E195969

CSA

C22.2 No. 18 (part numbers 1202-1211)

GENERAL PRODUCT INFORMATION

Trade Size: 2-1/2 in.

DRAWING DIMENSIONS

Dimension A: 3-15/32 in.
 Dimension B: 2-51/64 in.
 Thread Spec. C: 2-1/2 in. - 8 NPT
 Dimension D: 5/16 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 30
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 12.40
 Ship Carton Length (in.): 11.30
 Ship Carton Width (in.): 5.00
 Ship Carton Height (in.): 4.02
 Ctn Weight (Lbs.): 3.72
 UPC Number: 050169012079
 I2of5: 50050169012074