




INSULATED GROUNDING BUSHINGS

150° Insulated Grounding Bushings Lay-in Lug Malleable Iron
N/A

B42



Catalog #: 1212

APPLICATIONS

For use on threaded rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing
N/A

PRODUCT FEATURES

Lay-in and Feed-thru lug styles provide an easy means of inserting a ground wire
Dual rated aluminum grounding lugs may be used with copper or aluminum grounding conductors
Insuliner temperature rates at 150 degrees Celsius
Malleable iron construction insures mechanical protection for the raceway
Zinc electro plated for corrosion protection

UL LISTED

Standard 514B

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.
Min. Grounding Wire Capacity: #14 Sol.
Max Grounding Wire Capacity: #4 Str.

DRAWING DIMENSIONS

Dimension A: 1-5/32 in.
Dimension B: 9/16 in.
Dimension C: 1/2 in. - 14 NPS
Dimension D: 37/64 in.
Dimension E: 1-1/16 in.
Dimension F: 3/8 in.
Dimension G: 10-32 x 1/4 in.
Dimension H: 10-32 x 1/4 in.
Dimension I: 14-28 x 5/8 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 100
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 7.80
Ship Carton Length (in.): 10.00
Ship Carton Width (in.): 5.25
Ship Carton Height (in.): 5.19
Ctn Weight (Lbs.): 7.80
UPC Number: 050169012123
I2of5: 50050169012128