




**INSULATED GROUNDING BUSHINGS**

150° Insulated Grounding Bushings Feed-thru Lug Malleable Iron  
N/A

B42



Catalog #: 1236

**APPLICATIONS**

For use on threaded rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing  
N/A

**PRODUCT FEATURES**

Lay-in and Feed-thru lug styles provide an easy means of inserting a ground wire  
Dual rated aluminum grounding lugs may be used with copper or aluminum grounding conductors  
Insuliner temperature rates at 150 degrees Celsius  
Malleable iron construction insures mechanical protection for the raceway  
Zinc electro plated for corrosion protection

**UL LISTED**

Standard 514B

**CSA**

C22.2 No. 18

**GENERAL PRODUCT INFORMATION**

Trade Size: 4 in.  
Min. Grounding Wire Capacity: #6 Str.  
Max Grounding Wire Capacity: #250 MCM

**DRAWING DIMENSIONS**

Dimension A: 4-29/32 in.  
Dimension B: 15/16 in.  
Dimension C: 4 in. - 8 NPS  
Dimension D: 3-55/64 in.  
Dimension E: 1-3/4 in.  
Dimension F: 27-32 in.  
Dimension G: 5/16-24 x 7/16 in.  
Dimension H: 5/16-24 x 27/64 in.  
Dimension I: 5/8-18 x 11/16 in.

**PACKAGING**

Package Type: Carton  
Ship Carton Qty.: 5  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 113.40  
Ship Carton Length (in.): 8.25  
Ship Carton Width (in.): 6.00  
Ship Carton Height (in.): 5.50  
Ctn Weight (Lbs.): 5.67  
UPC Number: 050169012369  
I2of5: 50050169012364