

Anchor, PISA Nut, 1in threads Tripleye 50kip capacity

by CHANCE Utility
Catalog ID: 12585H

High strength Tripleye eyenut for 1" (25.4 mm) Pisa Rod.

- For use the Pisa style anchor rods
- Eyes are dropped forged for better strength and reliability
- Hot dipped galvanized per ASTM A153



* Representative image

Product Details

General

Coating	Galvanized
Eyenut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	50000 lb
Type	Power Installed Screw Anchor (PISA)
UPC	096359068402

Dimensions

Rod Diameter	1.000 in
Weight	1.989 lb

Logistics

Pallet Quantity	960 EA
Standard Package	25

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com