



# Anchor, Lead/Adapter, SS5, 8/10 X 3ft Thimbleye

by CHANCE Utility  
Catalog ID: 126541AE

Square Shaft (SS 5) Lead Section 3' (914 mm) long with 8" (203 mm) - 10" (254 mm) Helices with Guy Adapter Thimbleye in separate box.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

## Product Details

### General

Coating	Galvanized
Eye Nut Style	Thimbleye
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb
Torque Rating	5500 ft-lbs
Type	Lead Sections
UPC	096359567332

### Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Length	36.000 in

### Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com