



* Representative image

Rod, Expanding/Cross-Plate Anchor, 1-1/4in X 10ft Twineye

by CHANCE Utility
Catalog ID: 15129

Expanding/Cross-Plate Anchor Rod 1.25" (31.7 mm) Diameter Rod, 10' (3048 mm) long with Twineye.

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Product Details

General

Coating	Galvanized
Eye Nut Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	58000 lb
Type	Anchor Rod
UPC	096359068860

Dimensions

Length	120.000 in
Rod Diameter	1.250 in
Weight	42.042 lb

Logistics

Pallet Quantity	50 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com