




**RIGID THREADED HUBS - DIE CAST ZINC**

**Conduit Hub, Insulated Throat Die Cast Zinc**

**B33**



Catalog #: 1708

**APPLICATIONS**

For use with threaded rigid/IMC conduit to connect and bond conduit to a threadless opening in a box or enclosure  
May be used in wet or dry locations

**PRODUCT FEATURES**

Rugged metallic construction insures mechanical protection  
Insulated throat protects wires and reduces wire pulling effort  
O-ring seals the assembly and provides a raintight seal  
N/A

**UL LISTED**

Standard 514B, UL Listed E195969

**CSA**

C22.2 No. 18

**COMPLIANCES**

MSDS  
[www.hubbell-rtb.com/certifications/Hubbell-RACO\\_MSDS\\_for\\_WP\\_Boxes\\_and\\_Fittings,January\\_2015.pdf](http://www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf)

**GENERAL PRODUCT INFORMATION**

Trade Size: 2 in.

**DRAWING DIMENSIONS**

Dimension A: 1.895 in.  
Dimension B: 3.236 in.  
Dimension C: 2 in. - 11-1/2 NPT

**PACKAGING**

Package Type: Carton  
Ship Carton Qty.: 10  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 92.00  
Ship Carton Length (in.): 9.40  
Ship Carton Width (in.): 8.60  
Ship Carton Height (in.): 6.10  
Ctn Weight (Lbs.): 9.20  
UPC Number: 050169017081  
I2of5: 50050169017086