



BOLT, DA OVALEYE, 5/8in x 18in

by CHANCE Utility
Catalog ID: 19788

Double-arming ovaley eye bolt, 5/8" dia. x 18" long with 15" thread length. Includes three square nuts. Eye dimensions are 5/8" x 1 1/2" x 2". Rated tensile strength is 13,550 lbs. Galvanized steel per ASTM A-153. Manufactured in compliance with ANSI C135.4. RUS listed dy - Bolt, eye, double arming.



* Representative image

Product Details

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb
UPC	096359068990

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	18.00 in
Weight	2.27 lb

Certifications and Compliance

RUS Listed Reference	dy - Bolt, eye, double arming
----------------------	-------------------------------

Logistics

Pallet Quantity	600 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com