

15° Communication Standoff Bracket, 15"

by CHANCE Utility
Catalog ID: 1CSM15

15" Medium Duty Fiberglass 15° Communication Standoff Bracket



* Representative image

Product Details

General

Description - End Fitting	Communication clamp
Strength Rating - Minimum Ultimate, Longitudinal (L)	1200 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1800 lb
UPC	096359242321

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	15 in
Length	15.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 6.00 in • 8.00 in
Weight	4.2 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	216 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com