



# 15° Communication Standoff Bracket, 30"

by CHANCE Utility  
Catalog ID: 1CSM30

30" Medium Duty Fiberglass 15° Communication Standoff Bracket



\* Representative image

## Product Details

### General

Description - End Fitting	Communication clamp
Strength Rating - Minimum Ultimate, Longitudinal (L)	600 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359240693

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	30 in
Length	30.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> <li>• 6.00 in</li> <li>• 8.00 in</li> </ul>
Weight	6.1 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Pallet Quantity	140 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com