



# Horizontal Pin Standoff Bracket, 20"

by CHANCE Utility  
Catalog ID: 1SBH20H1

20" Heavy Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1" Plastics Coated Threads

## Product Details

### General

Description - End Fitting	Horizontal Pin
Material - Threads	1" Plastics Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1350 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2100 lb
UPC	096359067221

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	20 in
Length	20.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> <li>8.00 in</li> <li>10.00 in</li> </ul>
Weight	8.9 lb

### Logistics

Pallet Quantity	40 EA
Standard Package	2

For further technical assistance, please contact us

**Domestic Customer Service**  
 Hubbell Power Systems  
 210 N. Allen Centralia, MO 65240 USA  
 Phone: (573) 682-5521  
 Fax: (573) 682-8475  
 Email: hpscsc@hubbell.com

**International Customer Service**  
 Phone: +1-573-682-5521  
 Fax: +1-573-682-8516  
 Email: hpsintlcs@hubbell.com