



15° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 24"

by CHANCE Utility
Catalog ID: 1SBH24AMTB

24" Heavy Duty Fiberglass 15° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware



* Representative image

Product Details

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1900 lb
UPC	096359466376

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 8.00 in • 10.00 in
Weight	10.4 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com