

# 15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket W/ Hardware, 12"

by CHANCE Utility  
Catalog ID: 1SBM12DFCLH

12" Medium Duty Fiberglass 15° 7-Hole Dual Function Cloverleaf Cutout /  
Arrester Standoff Bracket W/ Hardware



\* Representative image

## Product Details

### General

Description - End Fitting	3 Position 7 Hole Clover Leaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1400 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1800 lb
UPC	096359464525

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	12 in
Length	12.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> <li>• 6.00 in</li> <li>• 8.00 in</li> </ul>
Weight	6.9 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Pallet Quantity	120 EA
Standard Package	5

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)