



Vertical Pin Standoff Bracket, 12"

by CHANCE Utility
Catalog ID: 1SBM12V1

12" Medium Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket
with 1" Plastisol Coated Threads



* Representative image

Product Details

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1400 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1800 lb
UPC	096359067504

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	12 in
Length	12.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	6.8 lb

Logistics

Pallet Quantity	144 EA
Standard Package	6

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com