



15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket, 18" (No Hardware)

by CHANCE Utility
Catalog ID: 1SBM18DFCL

18" Medium Duty Fiberglass 15° 7-Hole Dual Function Cloverleaf Cutout /
Arrester Standoff Bracket (No Hardware)



* Representative image

Product Details

General

Description - End Fitting	7-Hole 15° Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	950 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359464501

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 6.00 in • 8.00 in
Weight	7.7 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	144 EA
Standard Package	5

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com