



# 15° 1-Position Tear Drop Cutout / Arrester Standoff Bracket (No Hardware), 18"

by CHANCE Utility  
Catalog ID: 1SBM18TD

18" Medium Duty Fiberglass 15° 1-Position Single-Phase Tear Drop Cutout / Arrester Bracket (No Hardware)



\* Representative image

## Product Details

### General

Description - End Fitting	1 Position Tear Drop Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359396352

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> <li>• 6.00 in</li> <li>• 8.00 in</li> </ul>
Weight	10.0 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Standard Package	5
------------------	---

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscscs@hubbell.com](mailto:hpscscs@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)