



Horizontal Pin Standoff Bracket, 20"

by CHANCE Utility
Catalog ID: 1SBM20H4

20" Medium Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1.375" Lead Threads

* Representative image

Product Details

General

Description - End Fitting	Horizontal Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1100 lb
UPC	096359067856

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	20 in
Length	20.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 6.00 in • 8.00 in
Weight	6.2 lb

Logistics

Pallet Quantity	180 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com