



0° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 24"

by CHANCE Utility
Catalog ID: 1SBM24CTB

24" Medium Duty Fiberglass 0° 2-Position Cutout / Arrester Standoff Bracket w/Hardware



* Representative image

Product Details

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	500 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359408192

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	24 in
Length	24.00 in
Mounting Bolt Spacing	6.00 in
Weight	5.0 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	60 EA
Standard Package	6

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com