



# Suspension Standoff Bracket, 24"

by CHANCE Utility  
Catalog ID: 1SBM24S

24" Medium Duty Single-Phase Fiberglass Suspension Standoff Bracket



\* Representative image

## Product Details

### General

|  |              |
|--|--------------|
| Description - End Fitting                          | Suspension   |
| Strength Rating - Minimum Ultimate, Transverse (T) | 10000 lb     |
| Strength Rating - Minimum Ultimate, Vertical (V)   | 900 lb       |
| UPC  | 096359241416 |

### Dimensions

|                       |   |
|-----------------------|---|
| Diameter - Rod / Tube | 1.5 in  |
| Distance From Pole    | 24 in   |
| Length                | 24.00 in  |
| Mounting Bolt Spacing | <ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul> |
| Weight                | 6.7 lb  |

### Logistics

|                  |        |
|------------------|--------|
| Pallet Quantity  | 120 EA |
| Standard Package | 6      |

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)