



Catalog # 207

# 4 IN. SQUARE EXTENSION RING, WELDED, 2-1/8 IN. DEEP, SIX 1/2 IN. AND SIX 3/4 IN. KO'S

Add extra capacity with 4 In. square extension rings

## FEATURES

- Combination screw heads allow quick installation
- Welded construction
- Six 1/2 In. knockouts and six 3/4 In. knockouts
- 30.3 Cu. In. capacity
- Constructed from 1/16 In. pre-galvanized steel

## APPLICATIONS

Extension rings provide additional cubic capacity. May be used an outlet box for surface conduit.



## CERTIFICATIONS



## SPECIFICATIONS

UPC NUMBER:	050169002070
EA LENGTH/DEPTH (IN.):	2.188
EA WIDTH (IN.):	4.00
EA HEIGHT (IN.):	4.00
WT. EA. (LBS.):	0.650
PACKAGE TYPE:	LOOSE
PRODUCT UPC-A LABELED:	NO

## PACKAGING

CASE I2OF5:	50050169002075
STANDARD CARTON QTY:	25
MIN ORDER QTY:	25



All RACO single-gang, two-gang, 4 in. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at [www.ul.com](http://www.ul.com)

**600V** Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

