


**FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS**Straight Squeeze Connectors, Uninsulated Malleable Iron
N/A**B61**

Catalog #: 2104

APPLICATIONSFor use in dry locations to bond flexible metal conduit to a box or enclosure
N/A**PRODUCT FEATURES**All malleable iron construction insures mechanical protection for the raceway
Electro zinc plated for added corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation**CULUS**

UL Listed E195969

GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

DRAWING DIMENSIONS

Dimension A:	1-11/16 in.
Dimension B:	33/64 in.
Thread Spec. B:	1 in. - 11-1/2 NPT
Dimension C:	.935 in.
Dimension D:	1.364 - 1.408
Dimension E:	2-25/64 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	25
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	31.30
Ship Carton Length (in.):	10.00
Ship Carton Width (in.):	5.25
Ship Carton Height (in.):	4.31
Ctn Weight (Lbs.):	7.83
UPC Number:	050169021040
I2of5:	50050169021045