


FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS

Straight Squeeze Connectors, Uninsulated Malleable Iron

B61





Catalog #: 2105

APPLICATIONS

For use in dry locations to bond flexible metal conduit to a box or enclosure

PRODUCT FEATURES

All malleable iron construction insures mechanical protection for the raceway

Electro zinc plated for added corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

CULUS

UL Listed E195969

GENERAL PRODUCT INFORMATION

1-1/4 in. Trade Size:

DRAWING DIMENSIONS

Dimension A: Dimension B: 1-51/64 in.

33/64 in. 1-1/4 in. - 11-1/2 NPT Thread Spec. B:

Dimension C: Dimension D: 1.190 in 1.670 MAX Dimension E: 2-9/16 in.

PACKAGING

Package Type: Ship Carton Qty.: Carton 25 Product UPC-A Labeled: Weight (Lbs. Per/C): Ship Carton Length (in.): No 40.50 8.25 Ship Carton Width (in.): 8.25 Ship Carton Height (in.): Ctn Weight (Lbs.): 6.00 10.13

UPC Number: 12of5: 050169021057 50050169021052