


**EMT SET SCREW CONNECTORS**

Insulated Set Screw Connector, Steel

B03

Catalog #: 2123-8

APPLICATIONS

For use in dry locations to bond EMT conduit to a box or enclosure. RACO steel set screw connectors provide concrete-tight connections when taped.

PRODUCT FEATURES

- All steel construction insures mechanical protection for the raceway
- Tri-head screws may be installed using a slotted, Phillips, or Robertson head screwdriver
- 2-1/2 in. to 4 in. trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
- All components are zinc electroplated for corrosion protection
- 1/2 in. to 1 in. trade sizes have one set screw, 1-1/4 in. to 4 in. trade sizes have two set screws
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

UL LISTED

2-1/2" - 4" Standard 514B, File E195969, E195970

CULUS

1/2" - 2" Standard 514B, C22.2 # 18

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings_January_2015.pdf

GENERAL PRODUCT INFORMATION

Sub Class: Insulated
 Trade Size: 3/4 in.

DRAWING DIMENSIONS

Dimension A: 1.47 in.
 Dimension B: 1.08 in.
 Thread Spec. C: 3/4-14 NPSM
 Dimension D: .394 in.
 Dimension E: #12-28UNF

PACKAGING

Package Type: Carton
 Std. Pkg.: 1
 Ship Carton Qty.: 20
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 12.5
 Ship Carton Length (in.): 6.25
 Ship Carton Width (in.): 4.50
 Ship Carton Height (in.): 4.25
 Pallet Qty: 9600
 UPC Number: 050169212387