




4 IN. SQUARE WELDED BOXES - 1-1/2 IN. DEEP WITH ARMORED CABLE / METAL CLAD / FLEX CLAMPS

4 in. Square Bracketed Boxes, 1-1/2 in. Deep - Welded with Armored Cable/Metal Clad/Flex Clamps
600V, HM, UBS

A17



Catalog #: 213HWP

APPLICATIONS

RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles
Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices

PRODUCT FEATURES

Reference the Box Selection section in the front of this catalog for complete description of bracket types and features
Combination screw heads provide for faster installation
UBS Support - Welded to box, preset bend points to work with wall thickness 2-1/2" to 6"
N/A

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com
600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Armored Cable/Metal Clad/MCI-A/Flex

CONFIGURATION

Cable Priouts: 4
Bracket Type: H, for Metal or Wood Studs
Bracket Setback: 3/8 in.
Drawn or Welded: Welded
Raised Ground: No
Side Knockout(s): (4) 1/2 in. & (2) TKO®
Bottom Knockouts(s): (1) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-1/2 in.
Dimension C: 4-15/16 in.

PRODUCT MEASUREMENTS

Depth: 1-1/2 in.
Cubic Inches (cm3): 21.0 (344.1)
Wt. Ea. (Lbs.): 0.777
Product Length (in.): 2.06
Product Width (in.): 4.00
Product Height (in.): 4.92

PACKAGING

Minimum Pack Qty.: 20
Std. Pkg.: 20
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 77.70
Ship Carton Length (in.): 20.25
Ship Carton Width (in.): 8.50
Ship Carton Height (in.): 10.25
Ctn Weight (Lbs.): 38.85
Pallet Qty: 1600
UPC Number: 050169502136
I2of5: 50050169502131