



\* Representative image

# 15 Kv Class Elbow Arrester (2.55 kV MCOV)

by Hubbell Power Systems  
Catalog ID: 215ELA03

Deadfront Elbow Arrester, 15kV 2.55 MCOV

- To learn more about identifying the right Elbow Arrester on varying applications, visit our blog here.

## Product Details

### General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360537

### Dimensions

Height	6.600 in
Maximum Operating Altitude	6000 ft
Weight	3.700 lb

### Electrical Ratings

Duty Cycle	3 kV
MCOV	2.55 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 9.8 kV @ 1.5 kA</li> <li>• 10.3 kV @ 3 kA</li> <li>• 11 kV @ 5 kA</li> <li>• 12.3 kV @ 10 kA</li> <li>• 14.3 kV @ 20 kA</li> <li>• 18.5 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	8.5 kV
kV Class	15 kV

### Logistics

Pallet Quantity	160 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com