



* Representative image

15 kV Class Elbow Arrester (5.1 kV MCOV)

by Hubbell Power Systems
Catalog ID: 215ELA06

Deadfront Elbow Arrester, 15kV 5.1 MCOV

Product Details

General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360551

Dimensions

Height	6.600 in
Maximum Operating Altitude	6000 ft
Weight	3.700 lb

Electrical Ratings

Duty Cycle	6 kV
MCOV	5.1 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 19.5 kV @ 1.5 kA• 20.5 kV @ 3 kA• 22 kV @ 5 kA• 24.5 kV @ 10 kA• 28.5 kV @ 20 kA• 37 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	17.0 kV
kV Class	15 kV

Logistics

Pallet Quantity	160 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com