



\* Representative image

# 15kV Fused Elbow, 0.720 - 0.985 Cable insulation dia range, Hi- Tech® Fuse Connector

by Hubbell Power Systems  
Catalog ID: 215FEHB5

Fused Elbow, 15 kV, with Test Point, Cable Insulation Diameter range = 0.720 - 0.985 inches, 2/0 Solid or Compact and 1/0 Stranded or Compressed, Accepts Hi-Tech® EFX Current Limiting Fuses

## Product Details

### General

Connector Type	Hi-Tech® Fuse Connector
Integral Seal	No
PROBELOK® Connectors	No
Type	200A Loadbreak
UPC	096359658061
With Seal Kit	No
With Test Point	Yes

### Dimensions

Cable Insulation Diameter Maximum	0.985 in
Cable Insulation Diameter Minimum	0.720 in
Weight	7.0 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

### Conductor Related

Cable Insulation Diameter Range	0.720 - 0.985
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

### Logistics

Pallet Quantity	240 EA
Standard Package	1

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)