



* Representative image

15 kV, Load Break Elbow w/ Bimetal Contact

by Hubbell Power Systems
Catalog ID: 215LE57

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.760 - 1.135 inches, 4/0 Solid or Compacted and 3/0 Stranded or Compressed

Product Details

General

| | |
|----------------------|-------------------|
| Connector Type | Bi-Metal |
| Integral Seal | No |
| PROBELOK® Connectors | No |
| Type | 200Amp Load Break |
| UPC | 096359531678 |
| With Seal Kit | No |
| With Test Point | No |

Dimensions

| | |
|-----------------------------------|----------|
| Cable Insulation Diameter Maximum | 1.135 in |
| Cable Insulation Diameter Minimum | 0.760 in |
| Weight | 2.750 lb |

Electrical Ratings

| | |
|------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Basic Impulse Level | 95 kV |
| Corona Extinction (3pC) | 11 kV |
| Current Rating | 200 A |
| kV Class | 15 kV |

Conductor Related

| | |
|----------------------------------|---------------|
| Cable Insulation Diameter Range | 0.760 - 1.135 |
| Solid or Compacted Conductor | 4/0 |
| Stranded or Compressed Conductor | 3/0 |

Logistics

| | |
|------------------|--------|
| Pallet Quantity | 240 EA |
| Standard Package | 20 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com