



*Commercial, Industrial  
and Residential Electrical Products*

## 4 In. Square Box, Welded, 1-1/2 In. Deep with Nine 1/2 In. KO's and Five TKO's, BOX-LOC® MS Bracket, Flush

Catalog #:  
227



### FEATURE BENEFIT

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled. Includes our unique Box-Loc bracket.

### PRODUCT FEATURES

- TKO knockout design provides installation flexibility
- MS style BOX-LOC® flush bracket
- Welded construction
- Nine 1/2 In. knockouts and Five TKO knockouts
- 21.0 Cu. In. capacity
- RACO 978
- Acceptable in 2-hour fire rated walls

### APPLICATIONS

Suitable for use without a bonding jumper in circuits up to 600V.

### CERTIFICATIONS



### PRODUCT SPECIFICATIONS

UPC Number:	050169002278
Ea Length/Depth (in.):	1.750
Ea Width (in.):	5.625
Ea Height (in.):	4.500
Wt. Ea. (Lbs.):	0.834
Package Type:	Loose
Product UPC-A Labeled:	Yes

### SHIPPING

Case 12of5:	50050169002273
Standard Carton Qty:	25
Min Order Qty:	25



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at [www.ul.com](http://www.ul.com)

**600V**

Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, June 2021



A Division of Hubbell Incorporated (Delaware)

**RACO**  
3902 W. Sample St.  
South Bend, IN 46619  
574-234-7151  
[www.hubbell.com/raco/en](http://www.hubbell.com/raco/en)

