



**Commercial, Industrial
and Residential Electrical Products**

**4 In. Square Box, Welded, 1-1/2 In. Deep with NMSC
Clamps, Three 1/2 In. KO's and One TKO, BOX-LOC®,
MS Bracket, Flush**

**Catalog #:
228**



FEATURE BENEFIT

Shallow 1-1/2 In. deep steel box features built in clamps for {NMSC} nonmetallic sheathed cable

PRODUCT FEATURES

- Welded steel construction with "MS" BOX-LOC® bracket that can position box on either side of stud and nonmetallic sheathed cable clamps
- 4 In. square x 1-1/2 In. deep
- BOX-LOC® Bracket is a snap to install. Place the bracket on the open side of the stud first. Slots in the bracket engage the lip of the stud
- Provided with far-side support, model #978
- TKO® Knockouts allows for design and installation flexibility
- Supplied with five 1/2 In. and two 1/2-3/4 In. TKO® knockouts
- Combination Phillips/slotted screw heads
- 21.0 Cu. In. capacity
- Acceptable for use in 2-hour fire rated walls

APPLICATIONS

- RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles
- Square boxes are used where multiple conductors runs are split into two or more directions to bring power to a number of electrical devices

CERTIFICATION



PRODUCT SPECIFICATIONS

UPC Number:	050169002285
Ea Length/Depth (in.):	2.115
Ea Width (in.):	5.625
Ea Height (in.):	4.50
Wt. Ea. (Lbs.):	0.870
Package Type:	Loose
Product UPC-A Labeled:	Yes



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

PACKAGING

PK 12of5:	50050169002280
Standard Carton Qty:	25
Min Order Qty:	25

Revision 1, November 2019



RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

