



Catalog # 232HS

4 IN. SQUARE BOX, WELDED, 2-1/8 IN. DEEP, TEN 1/2 IN. KO'S AND SIX TKO'S

RAISED GROUND, 10 IN. #12 SOLID COPPER PIGTAIL, UBS, HM BRACKET

Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices. Built in bracket or supports speeds installation.

FEATURES

- UBS integrated support provides bracing on back of box for wall cavities between 2-1/2 In - 6 In. thickness,
- H/M bracket
- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 In. knockouts and Six TKO knockouts
- UL Listed
- 30.3 Cu. In. capacity
- Raised ground, 10 In. #12 solid copper pigtail
- Acceptable in 2-hour fire rated walls



APPLICATIONS

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled. Suitable for use without a bonding jumper in circuits up to 600V.

CERTIFICATIONS



SPECIFICATIONS

UPC NUMBER:	050169500385
EA LENGTH/DEPTH (IN.):	2.676
EA WIDTH (IN.):	4.91
EA HEIGHT (IN.):	4.03
WT. EA. (LBS.):	1.00
PACKAGE TYPE:	LOOSE
PRODUCT UPC-A LABELED:	NO

PACKAGING

CASE I2OF5:	50050169500380
STANDARD CARTON QTY:	25
MIN ORDER QTY:	25



All RACO single-gang, two-gang, 4 in. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

