



*Commercial, Industrial
and Residential Electrical Products*

4 In. Square Box, Welded, 2-1/8 In. Deep, Ten 1/2 In KO's & Six TKO's, Raised Ground, 8 In. #12 Stranded Copper Pigtail

Catalog #:
232SLD



FEATURE BENEFIT

Welded 4 In. square box for installing receptacles, switches or fixtures in walls or ceilings

PRODUCT FEATURES

- Combination screw heads allow quick installation
- Welded construction
- Eight 1/2 In. knockouts and four TKO knockouts
- 30.3 Cu. In. capacity
- Raised ground, 8 In. #12 stranded copper pigtail
- Acceptable in 2-hour fire rated walls

APPLICATIONS

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled. Suitable for use without a bonding jumper in circuits up to 600V.

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169995143
Ea Length/Depth (in.):	2.438
Ea Width (in.):	4.000
Ea Height (in.):	4.000
Wt. Ea. (Lbs.):	0.947
Package Type:	Loose
Product UPC-A Labeled:	Yes

SHIPPING

Case I2of5:	50050169995148
Standard Carton Qty:	25
Min Order Qty:	25



All RACO UL listed steel boxes are acceptable for use in 2-hour fire rated floor-ceiling and roof-ceiling assemblies, as well as 2 hr. fire rated bearing and non-bearing wood stud and steel stud walls. For additional information consult Fire Resistance Ratings ANSI/UL 263, Sec. III-6

Revision 1, October 2021



A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

