



* Representative image

35 kV Class Small Interface Elbow Arrester (19.5 kV MCOV)

by Hubbell Power Systems
Catalog ID: 235ELA24

Elbow Arrester, 35KV 19.5 MCOV, Mates with IEEE Std. 386, Interface 7B

Product Details

General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359433415

Dimensions

Height	13.700 in
Maximum Operating Altitude	6000 ft
Weight	5.200 lb

Electrical Ratings

Duty Cycle	24 kV
MCOV	19.5 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 71.5 kV @ 1.5 kA • 76.5 kV @ 3 kA • 82 kV @ 5 kA • 90.5 kV @ 10 kA • 106.5 kV @ 20 kA • 138 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	63.0 kV
kV Class	35 kV

Logistics

Pallet Quantity	64 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com