




ENTRANCE HEADS - ALUMINUM

Clamp Type for Rigid/IMC or EMT, Aluminum
N/A

B78



Catalog #: 2403

APPLICATIONS

For use to bring overhead electrical service into buildings
N/A

PRODUCT FEATURES

Lightweight aluminum body construction eases installation and provides corrosion resistance
Plastic insuliner snaps out easily for quick cable insertion

UL LISTED

Standard 514B, UL Listed E195972, E195973

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.

CONFIGURATION

Insulating Hole Diameter: 2 Holes 3/8 in. Dia.; 3 Holes 13/32 in. Dia.

DRAWING DIMENSIONS

Dimension A: 2-55/64 in.
Dimension B: 2-1/4 in.
Dimension C: 2-9/32 in.
Dimension D: 2-63/64 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 10
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 29.50
Ship Carton Length (in.): 7.60
Ship Carton Width (in.): 5.80
Ship Carton Height (in.): 5.80
Ctn Weight (Lbs.): 4.00
UPC Number: 050169024034
I2of5: 50050169024039