



*Commercial, Industrial  
and Residential Electrical Products*

## 4 In. Square Box, Welded, 2-1/8 In. Deep with AC/MC/Flex Clamps, Three 1/2 In. KO's and One TKO, TS Bracket, Flush

Catalog #:  
241



### FEATURE BENEFIT

Rugged steel box features built in clamps for {NMSC} nonmetallic sheathed cable

### PRODUCT FEATURES

- Welded steel construction with "TS" side-mount bracket with gauging tabs and recessed nailing spurs and nonmetallic sheathed cable clamps
- 4 In. square x 2-1/8 In. deep
- BX clamps provided for steel & alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- TKO® Knockouts allow for design and installation flexibility
- Supplied with three 1/2 In. and one 1/2-3/4 In. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 Cu. In. capacity
- Acceptable for use in 2-hour fire rated walls

### APPLICATIONS

- RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles
- Square boxes are used where multiple conductors runs are split into two or more directions to bring power to a number of electrical devices

### CERTIFICATION



### PRODUCT SPECIFICATIONS

UPC Number:	050169902417
Ea Length/Depth (in.):	2.188
Ea Width (in.):	4.313
Ea Height (in.):	7.00
Wt. Ea. (Lbs.):	1.080
Package Type:	Loose
Product UPC-A Labeled:	No

### PACKAGING

PK 12of5:	50050169902412
Standard Carton Qty:	25
Min Order Qty:	25



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at [www.ul.com](http://www.ul.com)

Revision 2, December 2021



A Division of Hubbell Incorporated (Delaware)

**RACO**  
3902 W. Sample St.  
South Bend, IN 46619  
574-234-7151  
[www.hubbell.com/raco/en](http://www.hubbell.com/raco/en)

