
# **NM CLAMP TYPE CONNECTORS**

## Clamp Type Cable Connectors Die Cast Zinc







Catalog #: 2864

#### APPLICATIONS

For use in dry locations to connect Nonmetallic Sheathed Cable (NMSC) to a box or enclosure For use with underground feeder (UF) cable to provide a non-watertight connection to meters and enclosures

## PRODUCT FEATURES

Rugged metallic construction will last the lifetime of the installation Rugged metallic construction will last the life of the installation N/A

## **UL LISTED**

Standard 514B, UL Listed E195972 Standard 514B, UL Listed E195972, E195971

### CSA

C22.2 No. 18

## COMPLIANCES

MSDS

www.hubbell-rtb.com/certifications/Hubbell-RACO MSDS for WP Boxes and Fittings, January 2015.pdf

## GENERAL PRODUCT INFORMATION

4 #12, 3 #12, 4 #10, 3 #10, 3 #8, 2 #8, 2 #6, 2 #4 Cable Size:

# DRAWING DIMENSIONS

Dimension A: Dimension B: 1.096 in. 1.44 in. Dimension C: 1.11 in. Dimension Da .50 in. Dimension E: 1.95 in.

1 in. - 11-1/2 NPSM NO. 10-24 x 1 in. Dimension F: Dimension G:

PACKAGING
Package Type:
Std. Pkg.: Carton Std. Pkg.: Ship Carton Qty.: Product UPC-A Labeled: Weight (Lbs. Per/C): Ship Carton Length (in.): Ship Carton Width (in.): 250 No 16.20 18.89 10.59 Ship Carton Height (in.): Ctn Weight (Lbs.): 6.81 40.50

UPC Number: 12of5: 050169028643 50050169028648