



**4 IN. ROUND CEILING FAN PANS, BOXES AND GORILLA-RING®**

**4 in. Round Ceiling Box - Drawn with Conduit KO's  
2-1/8 in. Depth, Old Work and New Work, 1/2 in. side KO's**

**A34**



Catalog #: 294

**APPLICATIONS**

RACO® Ceiling Support Boxes are specifically designed for ceiling fan and ceiling or wall light fixture support

**PRODUCT FEATURES**

- No protruding ground screw or fan mounting screws allows easy installation
- Metal protection plate eliminates debris or damage to wiring
- Easy to follow instructions and mounting hardware included
- 1/2" side knockouts
- #10-32, 1" long ceiling fan screws provided and provision for #8-32 fixture mounting screw
- Setback tab allows for easy installation of different wall thickness

**UL LISTED**

File E 195978

**US PATENTS**

7,148,420; 7,211,744

**RECOMMENDED MAX LOAD**

Ceiling Fan (Dynamic) Lbs.:	70
Fixture (Static) Lbs.:	70/150**

**CONFIGURATION**

Cable Priouts:	INSIDER®
Bracket Type:	FA, for Wood Joists
Bracket Setback:	1/2 to 1-1/4 in.
Drawn or Welded:	Drawn
Raised Ground:	Yes
Side Knockout(s):	(2) 1/2 in.
Bottom Knockouts(s):	(1) 1/2 in.

**DRAWING DIMENSIONS**

Dimension A:	2-1/8 in.
Dimension B:	4 in.
Dimension C:	3-1/2 in.
Dimension D:	1/2 in.
Dimension E:	1-3/4 in.

**PRODUCT MEASUREMENTS**

Depth:	2-18 in.
Cubic Inches (cm3):	22.3 (365.4)
Wt. Ea. (Lbs.):	1.350
Product Length (in.):	2.75
Product Width (in.):	4.25
Product Height (in.):	4.13

**PACKAGING**

Minimum Pack Qty.:	10
Std. Pkg.:	10
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	135.00
Ship Carton Length (in.):	14.50
Ship Carton Width (in.):	4.75
Ship Carton Height (in.):	9.00
Ctn Weight (Lbs.):	13.50
Pallet Qty:	960
UPC Number:	050169002940
I2of5:	50050169002945