



BOLT, OVALEYE, 3/4in x 20in

by CHANCE Utility
Catalog ID: 29990



Ovaleye bolt, 3/4" dia. x 20" long with 6" thread length. Includes one square nut. Eye dimensions are 5/8" x 1 1/2" x 2". Rated tensile strength is 20,050 lbs. Galvanized steel per ASTM A-153. RUS listed o - Bolt, eye, oval

* Representative image

Product Details

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb
UPC	096359486237

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	20.00 in
Length - Threaded Area	6
Weight	3 lb

Logistics

Carton Quantity	15 EA
Pallet Quantity	720 EA

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com