

2ABV-350MS

by CMC

Catalog ID: 2ABV-350MS



General purpose transformer connectors, Dual rated connectors for Aluminum or Copper conductors

- Compact design relieves cantilever stress.
- Clear Plated for low contact resistance.
- Fully tested to ANSI C119.4 for Class "A" connectors.
- Designed for installation on standard NEMA bolt holes.
- Fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Supplied with aluminum radial-tipped set-screws.

Product Details

General

Material	Aluminum Alloy, 6061-T6
Type	Bolted Lugs & Terminals
UPC	192663138531

Dimensions

Length	3.25 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	2