



15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket, 48" 2-Phase

by CHANCE Utility
Catalog ID: 2SBH48CLCL

48" Heavy Duty Fiberglass 15° 7-Hole Dual Function Cloverleaf Two-Phase
Cutout / Arrester Standoff Bracket



* Representative image

Product Details

General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1850 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2200 lb
UPC	096359366638

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	48 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 5.00 in • 6.00 in • 8.00 in
Weight	23.7 lb

Electrical Ratings

Phase	2-Phase
-------	---------

Logistics

Pallet Quantity	5 EA
Standard Package	5

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com