



Horizontal Pin Standoff Bracket, 48" Two-Phase

by CHANCE Utility
Catalog ID: 2SBH48HH1

48" Heavy Duty Fiberglass Two-Phase Horizontal Pin Standoff Bracket with 1" Plastisol Coated Threads



* Representative image

Product Details

General

Description - End Fitting	Horizontal Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2250 lb
UPC	096359069157

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	48 in
Length	48.00 in
Mounting Bolt Spacing	• 5.00 in • 6.00 in • 8.00 in
Weight	17.6 lb

Logistics

Pallet Quantity	20 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com